

## EX-TEC® PM 580/550/500/400

### Release Notes V1.100 (06/05/2024)

#### Compatibility

- fully compatible with:
  - **GasCom** software software version **V1.3.0**
  - Test set **ATS 503/501** firmware version **V1.100**
- limited compatibility with:
  - **GasCom** software software versions older than **V1.3.0**
  - Test set **ATS 503/501** firmware version up to **V1.010**

#### Improvements and new features

- Measurement:
  - Automatic recording possible
- Device inspection:
  - Acceptance possible of device inspections from the same day
  - Guided device inspection can be performed at any time even if guided device inspection has been deactivated via GasCom software (Difference compared with “guided device inspection activated”: due dates are not displayed)
- Protocols:
  - The number of device inspections and recordings that can be saved has been increased to 500 each
  - Presentation of device inspection protocols standardised for device and ATS test set
- Saving device inspections and recordings
  - A decision can be made whether the oldest protocols are automatically deleted when the memory is full
- User:
  - Number of possible users increased to 100
  - Display of user list possible
- Application “Structure”:
  - Stability of zero point optimised
- PM 400, gas type Nonan:
  - Adjustment and test of sensitivity now with 0.28 vol. % C<sub>9</sub>H<sub>20</sub> in synth. air (previously: 0.22 vol. %); substitute test gas unchanged 0.30 vol. % C<sub>3</sub>H<sub>8</sub> in synth. air
- Automatic or manual key lock possible
- New symbol for data exchange
- Display of remaining capacity optimised for disposable battery/rechargeable battery